



Fig. 19. Composants du filtre à air électronique (illustré : modèle à deux cellules).

M18846D

REPLACEMENT PARTS (TABLE 4)/EXPLODED VIEW (FIG. 19)

Table 4. Replacement Parts.

No.	Description	Nominal Return Air Opening				
		16 x 20 in. (406 x 508 mm)	16 x 25 in. (406 x 635 mm)	20 x 12-1/2 in. (508 x 318mm)	20 x 20 in. (508 x 508 mm)	20 x 25 in. (508 x 635 mm)
1	F300 Door includes No. 2	32007528-003	32007528-003	N/A	32007528-002	32007528-002
2	Test Button Assembly	137980A (1)	137980A (1)	137980A (1)	137980A (1)	137980A (1)
3	Electronic Cell	FC37A1114 (2)	FC37A1130 (2)	FC37A1064 (1)	FC37A1049 (2)	FC37A1064 (2)
4	Cell Handle	137266 (2)	137266 (2)	137266 (1)	137266 (2)	137266 (1)
5	Prefilter (without spring clips)	209989 (2)	203368 (2)	203369 (1)	203370 (2)	203369(2)
6	Cell Key	136518 (1)	136518 (1)	136518 (1)	136518 (1)	136518 (1)
7	F300 Power Box Assembly Series Two ^b . Includes No. 8– 20. 120V, 60 Hz. White Cover.	208418J (1)	208417S (1)	208419D ^d	208418H (1)	208417R (1)
	240V, 60 Hz ^c			208419B ^b		
8	Switch	203321 (1)	203321 (1)	203321 (1)	203321 (1)	203321 (1)
10	F300 Power Supply, Series Two ^b . 120V, 60 Hz	208045J (1)	208045G(1)	208045G	208045G (1)	208045G (1)
	240V, 60 Hz	N/A ^c	N/A ^c	N/A	N/A ^c	N/A ^c
11	Interlock Bracket and Switch	4074ETG (1)	4074ETG (1)	4074ETG (1)	4074ETG (1)	4074ETG (1)
12	W8600 Terminal Strip	Supplied with W8600F				
13	Terminal Board Assembly Front	203329B (1)	203329B (1)	N/A	N/A	203329B (1)
14	Terminal Board Assembly Rear	203329A (1)	203329A (1)	N/A	203329A (1)	203329A (1)
17	Line Cord	4074ETD (1)	4074ETD (1)	4074ETD (1)	4074ETD (1)	4074ETD (1)
19	Neon Assembly	4074EYS (1)	4074EYS (1)	4074EYS (1)	4074EYS (1)	4074EYS (1)
20	Airflow Switch, pin connection	4074ETH (1)	4074ETH (1)	4074ETH (1)	4074ETH (1)	4074ETH (1)
20	Airflow Switch, plug connection	4074EZB (1)	4074EZB (1)	N/A	4074EZB (1)	4074EZB (1)
21	FC37A Bag Assembly for cell repair. Contains: 2 Connector Clips, 1 Terminal Board and instructions	4074EHG	4074EHG	4074EHG	4074EHG	4074EHG
22	Post Filter (optional)	50000293-001	50000293-002	50000293-004	50000293-003	50000293-004

^b Series Two compatible with W8600F.

^c Use 203365A Conversion Kit for charging 120V, 60 Hz model to 240V, 60 Hz.

^d Change from brown cover to white cover as a running change. Use original cover for color match.

(#) = Quantity required per unit.

N/A = Not available as merchandised part.

PARTS AND ACCESSORIES NOT ILLUSTRATED (TABLE 5)

Table 5. Parts and Accessories Not Illustrated.

Description	Nominal Return Air Opening				
	16 x 20 in. (406 x 508 mm)	16 x 25 in. (406 x 635 mm)	20 x 12-1/2 in. (508 x 318)	20 x 20 in. (508 x 508 mm)	20 x 25 in. (508 x 635 mm)
Air Cleaner Cabinet Gasket Kit	32002109-001	32002109-001	32002109-001	32002109-001	32002109-001
Ionizer Wires (Multiples of 5)	136434BA	136434BA	136434AA	136434AA	136434AA
Premier White® AIRWATCH® Indicator	W8600A1007	W8600A1007	W8600A1007	W8600A1007	W8600A1007
Premier White® Air Cleaner Monitor	W8600F1014	W8600F1014	W8600F1014	W8600F1014	W8600F1014
240V Conversion Kit	203365A	203365A	N/A	203365A	203365A

(#) = Quantity required per unit.

N/A = Not available as merchandised part.

Obsolete (available while supplies last)